



FILO OVALE / OVAL WIRE / OVAL DRAHT / FIL OVALE

ESEMPIO D'ORDINE / ORDERING EXAMPLE / BESTELLBEISPIEL / EXAMPLE DE COMMANDE: (25) MBL 19 - 051
CONSEGNA DA MAGAZZINO / DELIVERY FROM STOCK / LIEFERUNG AB LAGER / DISPONIBLE SUR STOCK

D _H	D _d	L ₀	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	R	A		B		C		D	
					25% L ₀	40% L ₀	50% L ₀	f _b				
mm	mm	mm		N / mm	N	mm	N	mm	N	mm	N	mm
9.5	4.7	25	MBL 10 - 025	14.4	91	6.3	144	10.0	180	12.5	194	13.5
		32	MBL 10 - 032	12.3	98	8.0	157	12.8	197	16.0	215	17.5
		38	MBL 10 - 038	9.8	93	9.5	149	15.2	186	19.0	204	20.8
		44	MBL 10 - 044	8.8	97	11.0	155	17.6	194	22.0	210	23.9
		51	MBL 10 - 051	7.5	96	12.8	153	20.4	191	25.5	217	28.9
		64	MBL 10 - 064	4.9	78	16.0	125	25.6	157	32.0	177	36.1
		76	MBL 10 - 076	3.8	72	19.0	116	30.4	144	38.0	164	43.2
		305	MBL 10 - 305	1.2	92	76.3	146	122.0	183	152.5	214	178.7
13	7	25	MBL 13 - 025	18.9	119	6.3	189	10.0	236	12.5	249	13.2
		32	MBL 13 - 032	15.4	123	8.0	197	12.8	246	16.0	277	18.0
		38	MBL 13 - 038	13.5	128	9.5	205	15.2	257	19.0	284	21.0
		44	MBL 13 - 044	11.8	130	11.0	208	17.6	260	22.0	283	24.0
		51	MBL 13 - 051	10.0	128	12.8	204	20.4	255	25.5	287	28.7
		64	MBL 13 - 064	7.6	122	16.0	195	25.6	243	32.0	272	35.8
		76	MBL 13 - 076	5.9	112	19.0	179	30.4	224	38.0	252	42.7
		89	MBL 13 - 089	4.8	107	22.3	171	35.6	214	44.5	242	50.4
		102	MBL 13 - 102	3.4	87	25.5	139	40.8	173	51.0	199	58.4
		305	MBL 13 - 305	1.6	122	76.3	195	122.0	244	152.5	275	172.0
16	8.7	25	MBL 16 - 025	30.4	144	6.3	229	10.0	286	12.5	291	12.7
		32	MBL 16 - 032	22.5	180	8.0	288	12.8	360	16.0	374	16.6
		38	MBL 16 - 038	18.9	180	9.5	287	15.2	359	19.0	378	20.0
		44	MBL 16 - 044	16.8	185	11.0	296	17.6	370	22.0	393	23.4
		51	MBL 16 - 051	15.4	197	12.8	314	20.4	393	25.5	413	26.8
		64	MBL 16 - 064	10.5	168	16.0	269	25.6	336	32.0	349	33.2
		76	MBL 16 - 076	9.8	186	19.0	298	30.4	372	38.0	410	41.8
		89	MBL 16 - 089	8.4	187	22.3	299	35.6	374	44.5	408	48.6
		102	MBL 16 - 102	7.7	196	25.5	314	40.8	393	51.0	427	55.5
		115	MBL 16 - 115	5.9	170	28.8	271	46.0	339	57.5	367	62.2
305	MBL 16 - 305	2.5	191	76.3	305	122.0	381	152.5	427	170.9		
19.5	9.5	25	MBL 19 - 025	53.0	334	6.3	530	10.0	663	12.5	673	12.7
		32	MBL 19 - 032	43.1	345	8.0	552	12.8	690	16.0	733	17.0
		38	MBL 19 - 038	34.3	326	9.5	521	15.2	652	19.0	696	20.3
		44	MBL 19 - 044	30.4	334	11.0	535	17.6	669	22.0	714	23.5
		51	MBL 19 - 051	25.5	326	12.8	520	20.4	650	25.5	699	27.4
		64	MBL 19 - 064	20.6	330	16.0	527	25.6	659	32.0	715	34.7
		76	MBL 19 - 076	16.2	308	19.0	492	30.4	616	38.0	687	42.4
		89	MBL 19 - 089	14.2	317	22.3	506	35.6	632	44.5	694	48.9
		102	MBL 19 - 102	12.2	311	25.5	498	40.8	622	51.0	691	56.6
		115	MBL 19 - 115	11.0	317	28.8	506	46.0	633	57.5	705	64.1
		127	MBL 19 - 127	9.8	312	31.8	498	50.8	622	63.5	703	71.7
		140	MBL 19 - 140	8.3	291	35.0	465	56.0	581	70.0	662	79.8
		152	MBL 19 - 152	7.2	274	38.0	438	60.8	547	76.0	618	85.9
		305	MBL 19 - 305	4.1	313	76.3	500	122.0	625	152.5	688	167.8

Note: 1 N = 0,102 Kg (force)



D _H	D _d	L ₀	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	R	A		B		C		D			
					25% L ₀		40% L ₀		50% L ₀		f _b			
					N	mm	N	mm	N	mm	N	mm		
25.5	13	25	MBL 26 - 025	107.9	680	6.3	1079	10.0	1349	12.5	1360	12.6		
		32	MBL 26 - 032	80.4	643	8.0	1029	12.8	1286	16.0	1294	16.1		
		38	MBL 26 - 038	62.8	597	9.5	955	15.2	1193	19.0	1199	19.1		
		44	MBL 26 - 044	52.0	572	11.0	915	17.6	1144	22.0	1191	22.9		
		51	MBL 26 - 051	43.1	552	12.8	879	20.4	1099	25.5	1177	27.3		
		64	MBL 26 - 064	35.3	565	16.0	904	25.6	1130	32.0	1175	33.3		
		76	MBL 26 - 076	29.4	559	19.0	894	30.4	1117	38.0	1161	39.5		
		89	MBL 26 - 089	24.5	546	22.3	872	35.6	1090	44.5	1169	47.7		
		102	MBL 26 - 102	21.6	551	25.5	881	40.8	1102	51.0	1218	56.4		
		115	MBL 26 - 115	18.6	536	28.8	856	46.0	1070	57.5	1157	62.2		
		127	MBL 26 - 127	17.2	547	31.8	874	50.8	1092	63.5	1194	69.4		
		140	MBL 26 - 140	15.7	550	35.0	879	56.0	1099	70.0	1207	76.9		
		152	MBL 26 - 152	14.7	559	38.0	894	60.8	1117	76.0	1220	83.0		
		178	MBL 26 - 178	12.7	565	44.5	904	71.2	1130	89.0	1252	98.6		
203	MBL 26 - 203	10.8	549	50.8	877	81.2	1096	101.5	1209	111.9				
305	MBL 26 - 305	7.4	565	76.3	903	122.0	1129	152.5	1224	165.4				
32	16	38	MBL 32 - 038	88.3	839	9.5	1342	15.2	1678	19.0	1695	19.2		
		44	MBL 32 - 044	76.5	842	11.0	1346	17.6	1683	22.0	1714	22.4		
		51	MBL 32 - 051	60.8	778	12.8	1240	20.4	1550	25.5	1569	25.8		
		64	MBL 32 - 064	49.0	784	16.0	1254	25.6	1568	32.0	1622	33.1		
		76	MBL 32 - 076	41.2	783	19.0	1252	30.4	1566	38.0	1644	39.9		
		89	MBL 32 - 089	35.3	787	22.3	1257	35.6	1571	44.5	1663	47.1		
		102	MBL 32 - 102	30.4	775	25.5	1240	40.8	1550	51.0	1654	54.4		
		115	MBL 32 - 115	27.5	792	28.8	1265	46.0	1581	57.5	1680	61.1		
		127	MBL 32 - 127	23.5	747	31.8	1194	50.8	1492	63.5	1603	68.2		
		140	MBL 32 - 140	21.6	756	35.0	1210	56.0	1512	70.0	1635	75.7		
		152	MBL 32 - 152	19.6	745	38.0	1192	60.8	1490	76.0	1613	82.3		
		178	MBL 32 - 178	17.7	788	44.5	1260	71.2	1575	89.0	1722	97.3		
		203	MBL 32 - 203	14.7	747	50.8	1194	81.2	1492	101.5	1620	110.2		
		254	MBL 32 - 254	12.7	806	63.5	1290	101.6	1613	127.0	1751	137.9		
305	MBL 32 - 305	9.8	748	76.3	1196	122.0	1495	152.5	1605	163.8				
38.5	19.5	51	MBL 38 - 051	81.4	1042	12.8	1661	20.4	2076	25.5	2141	26.3		
		64	MBL 38 - 064	62.8	1005	16.0	1608	25.6	2010	32.0	2079	33.1		
		76	MBL 38 - 076	51.0	969	19.0	1550	30.4	1938	38.0	2035	39.9		
		89	MBL 38 - 089	43.1	961	22.3	1534	35.6	1918	44.5	2043	47.4		
		102	MBL 38 - 102	36.3	926	25.5	1481	40.8	1851	51.0	1986	54.7		
		115	MBL 38 - 115	32.4	933	28.8	1490	46.0	1863	57.5	1989	61.4		
		127	MBL 38 - 127	29.4	935	31.8	1494	50.8	1867	63.5	2002	68.1		
		140	MBL 38 - 140	27.0	945	35.0	1512	56.0	1890	70.0	2074	76.8		
		152	MBL 38 - 152	24.5	931	38.0	1490	60.8	1862	76.0	2021	82.5		
		178	MBL 38 - 178	21.6	961	44.5	1538	71.2	1922	89.0	2115	97.9		
		203	MBL 38 - 203	18.6	945	50.8	1510	81.2	1888	101.5	2052	110.3		
		254	MBL 38 - 254	14.7	933	63.5	1494	101.6	1867	127.0	2058	140.0		
		305	MBL 38 - 305	10.8	824	76.3	1318	122.0	1647	152.5	1772	164.1		
		51	25.5	64	MBL 51 - 064	156.9	2510	16.0	4017	25.6	5021	32.0	5036	32.1
76	MBL 51 - 076			132.4	2516	19.0	4025	30.4	5031	38.0	5455	41.2		
89	MBL 51 - 089			114.7	2558	22.3	4083	35.6	5104	44.5	5517	48.1		
102	MBL 51 - 102			98.1	2502	25.5	4002	40.8	5003	51.0	5366	54.7		
115	MBL 51 - 115			87.3	2514	28.8	4016	46.0	5020	57.5	5430	62.2		
127	MBL 51 - 127			77.5	2465	31.8	3937	50.8	4921	63.5	5379	69.4		
140	MBL 51 - 140			69.6	2436	35.0	3898	56.0	4872	70.0	5345	76.8		
152	MBL 51 - 152			64.7	2459	38.0	3934	60.8	4917	76.0	5299	81.9		
178	MBL 51 - 178			53.0	2359	44.5	3774	71.2	4717	89.0	5199	98.1		
203	MBL 51 - 203			47.1	2393	50.8	3825	81.2	4781	101.5	5299	112.5		
254	MBL 51 - 254			37.5	2381	63.5	3810	101.6	4763	127.0	5295	141.2		
305	MBL 51 - 305			31.4	2396	76.3	3831	122.0	4789	152.5	5335	169.9		
63	38			76	MBL 63 - 076	189.3	3597	19.0	5755	30.4	7193	38.0	7269	38.4
				89	MBL 63 - 089	156.9	3499	22.3	5586	35.6	6982	44.5	7217	46.0
		102	MBL 63 - 102	133.4	3402	25.5	5443	40.8	6803	51.0	7044	52.8		
		115	MBL 63 - 115	116.7	3361	28.8	5368	46.0	6710	57.5	6967	59.7		
		127	MBL 63 - 127	104.0	3307	31.8	5283	50.8	6604	63.5	7010	67.4		
		140	MBL 63 - 140	93.1	3259	35.0	5214	56.0	6517	70.0	6955	74.7		
		152	MBL 63 - 152	84.3	3203	38.0	5125	60.8	6407	76.0	6904	81.9		
		178	MBL 63 - 178	72.6	3231	44.5	5169	71.2	6461	89.0	7151	98.5		
		203	MBL 63 - 203	62.8	3190	50.8	5099	81.2	6374	101.5	6851	109.1		
		254	MBL 63 - 254	47.1	2991	63.5	4785	101.6	5982	127.0	6603	140.2		
		305	MBL 63 - 305	38.2	2915	76.3	4660	122.0	5826	152.5	6223	162.9		